



IONOMR PRODUCT OFFERINGS:

AEM Catalyst Coated Membranes / Membrane Electrode Assemblies

**2386 East Mall - Suite 111
Vancouver, BC Canada
V6T 1Z3**

CCMs / MEAs

AEM Catalyst Coated Membranes / Membrane Electrode Assemblies

Ionomr Innovations, Inc., provides ion-exchange materials and core components for electrolyzers as a convenient assessment tool for evaluation and integration of its anion exchange membrane and ionomer + (Aemion+) technologies:

Catalyst coated membranes

in standard and custom sizes, coated with standardized catalyst layers

Membrane electrode assemblies

in standard and custom sizes in multi-layer configurations comprising standardized catalyst layers, framing materials, and gas diffusion layers.





Figure 1. Performance of AF2-HWP8-75 in 1M KOH and 80 °C: polarization curve (top) and voltage at constant 1 A/cm² for 120 hours (bottom)

Water Electrolysis CCMs

Active area: 5, 25, 50 cm²
Custom configurations up to 100 cm²

Membranes: AF2-HWP8-75 & AF3-HWK9-75

Ionomer: Aemion® AP2-HNN8
16wt% Ionomers on cathode and 18wt% on anode in total solids

Catalysts: **Anode:**
NiFeOx, 72.7 % NiFe in parent compound;
2.0 mg/cm²
Sintered Ni Felt PTL

Cathode: Pt/C, 36.9 % Pt in parent compound;
0.4 mg/cm²
Carbon Paper GDL

***NOTE:** Complete MEA to be exchanged according to membrane handling procedure prior to use. Do not contact the membrane or CCM with DI water (dip/rinse included) after exchange*

Water electrolysis MEAs

Option 1: (Coming soon) Aemion® membrane coated with standard anode and cathode catalyst layers (CCM)

Option 2: Gas diffusion electrodes (GDE) - PTL coated with standard anode and cathode catalyst layers